



# **e-STUDIO120** | **e-STUDIO150**

Versatile Workgroup Solutions

**TOSHIBA**

Don't copy. Lead.

## A VERSATILE COPIER/PRINTER WITH FULL COLOR SCANNING CAPABILITIES



e-STUDIO120/150  
Control Panel



e-STUDIO120/150  
Base Configuration



e-STUDIO120/150  
Fully Configured

Toshiba's e-STUDIO120/150 is an economical imaging solution that offers outstanding copying, printing, and full color scanning functionality, right out of the box.

It features Scan Once/Print Many and Full Color Scanning capabilities to easily convert paper documents into electronic form for paperless distribution or archives. Color scanning functions can be set to five different settings directly linked to the "SCAN" button. The default menu functions include Scan-to-File, Scan-to-Email, Scan-to-Fax, Scan-to-OCR, and Scan-to-Word.

The e-STUDIO120/150 copies 12 Pages Per Minute (PPM) and 15 PPM respectively, with a First Copy Out Time of 9.6 Seconds. Flexible paper handling features include 8½" x 14" Maximum Paper Size, a Single 250-Sheet Cassette and 50-Sheet Bypass Tray, and an optional second 250-Sheet Cassette and 30-Sheet Auto Document Feeder.

The e-STUDIO120/150 has a Maximum Print Speed of 12 PPM at 600 dpi Resolution with a standard Parallel GDI Print Driver. It also supports all popular Windows® 95, 98, Me, 2000, XP, and Windows® NT 4.0 operating systems.

See the versatile e-STUDIO120/150 digital copier at your local Toshiba Dealer, today.

## SPECIFICATIONS

### Basic Composition

Copying Process	Digital—Dry Electrostatic Transfer
Original Reading Method	3 Colors—CCD Line Sensor
Type	Desktop
Copy Resolution	600 dpi/256 Gradation
Copying Speed	12/15 PPM
Max. Monthly Copy Volume	12,000/15,000 Pages
First Copy Out Time	9.6 Sec.
Warm-up Time	30 Sec.
Multiple Copying	Up to 99
Acceptable Paper Size	Tray 1/2—Letter, Legal, 8.5" x 5.5" (15-21 Lbs.) Bypass—Letter, Legal, 8.5" x 5.5", 3.3" x 5.5" (14-34 Lbs.)
Special Media	Bypass—Transparency Film and Envelope
Reduction/Enlargement	25%–400%
Image Density Control	Mode: Auto/Manual/Photo
Paper Supply	Standard 250-Sheet Cassette Standard 50-Sheet Bypass Optional 250-Sheet Cassette
Dimensions	20.4" x 18.5" x 11.6" (W x D x H)
Weight	35 Lbs.
PM Cycle	25K
Drum Yield	25K
Developer Yield	25K
Toner Yield	8K
Power Supply	115 Volts

### Special Features

Auto Exposure
Manual Exposure
Toner Save Mode
User Simulation
Time Out to Auto Clear
Time Out to Preheat
Time Out to Auto Shut-Off
Manual Exposure Adjustment
ADF Exposure Adjustment

### Copy Options

#### MR-2014—Automatic Document Feeder

Feeder Capacity	30-Sheet (14–23.9 Lbs.)
Original Size	Letter to Legal

#### MY-1019—2nd Cassette

Paper Supply	250-Sheet (15–21 Lbs.)
Paper Size	Letter, Legal, 8.5" x 5.5"

### Print Features

Standard Printer	GDI Printing
Maximum Print Speed	12 PPM
Print Memory	8 MB
Operating System Support Interface	Windows® 95, 98, Me, 2000, XP, Windows® NT 4.0 Parallel IEEE1284, USB

### Scanning Features

Standard Full Color Scanner Speed	600 x 1,200 dpi TWAIN/WIA (only Windows® XP) Maximum 2.88ms/line
Interface	USB
Scanner Utility Software	Button Manager/Desktop Document Manager

### Conformance to Standard

Environmental	Energy Star
Safety Standard	cUL, FDA
Emission/Immun.	FCC (Part15 Class B, ICES-003)
Noise	Idling 40dB, Copying 63dB

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 5% coverage, letter-size page.

**TOSHIBA**  
COPY • FAX • PRINT