

Your office never looked
more productive.

Medium Workgroup



e-STUDIO™170F



17



Workgroup



Black & White

TOSHIBA
Don't copy. Lead.

Designed to make your job easier.

The Toshiba e-STUDIO170F is ready to go, right out of the box. It includes a standard USB interface, Windows PC printing, scanning, and a convenient setup utility that allows users to program the fax machine from a PC.

Separate drum and toner components provide for a full life of the drum and easy access to supplies that are user replaceable. With everything the e-STUDIO170F has to offer, it is surprisingly compact. This small but feature-rich machine is the perfect choice for small to medium offices and workgroups. It may be small, but it's sure to increase productivity in a big way.



When you consider everything the e-STUDIO170F has to offer, why consider anything else?

e-STUDIO™ 170F

The Toshiba e-STUDIO170F

A small facsimile system that thinks big.

The Toshiba e-STUDIO170F is the perfect facsimile system to help make small and medium sized workgroups more productive. This hardworking, multifunction unit can fax, print, copy and scan. It faxes at an impressive rate of 3 seconds per page and prints at a speed of 17 pages per minute. Add to that a Super G3, 33.6 Kbps modem, 7 MB of memory, and JBIG compression. And that's just the beginning.



e-STUDIO™ 170F



38
programmable,
one-touch
dialing keys

Productivity is on the rise.

Any small to medium office or workgroup can produce even more thanks to the e-STUDIO170F. There are 38 programmable, one-touch dialing keys so you can send faxes to commonly used locations. In addition, the 188 location dialer allows you to take advantage of 150 abbreviated/alphabet speed dialing numbers. An automatic redial makes sure faxes get to where they are going. Transmission is as impressive as dialing, with dual access, auto/manual contrast control, delayed transmission, batching and error correction, just to name a few of the e-STUDIO170F capabilities.

Features & Benefits

OUTSTANDING PERFORMANCE

- Super G3, 33.6 Kpbs Modem
- 3 Sec/Page Fax Transmission
- 7 MB Memory
- JBIG Compression
- 17 PPM Print Speed

EXCEPTIONAL PRODUCTIVITY

- Automatic Redial
- 38 One-Touch Keys
- 150 Abbreviated/Alphabet Dialing
- 188 Location Autodialer

FLEXIBILITY

- Standard Multifunction Features
- Fax
- PC Scanning
- 600 dpi Windows Printing
- Convenience Copy
- Compact Footprint

EASY TO USE

- Standard Toshiba Viewer Software
- Windows Printing, Scanning and Device Setup Utility
- Separate Drum and Toner Components
- User Replaceable Supplies

Fax, copy, print, you name it.

Whatever features you're looking for in a facsimile system, the e-STUDIO170F is sure to have them. The standard multifunction features include fax, PC scan, and 600 dpi Windows® printing. Management features include account codes, department codes, confirmation reports, power save mode and remote terminal identification. If you're wondering whether or not the e-STUDIO170F can handle the job, you should know that it has a 40-sheet automatic document feeder, letter/legal output capabilities, collated printing, single sheet bypass and 250-sheet paper cassette. And in case that's not enough, you can opt for an additional 500-sheet cassette.

40
sheet
automatic
document
feeder

"You can opt for an additional
500-sheet cassette"

Fax
Rate: **3**
seconds
per page


The e-STUDIO170F can handle letter or legal sized paper with its standard 250-sheet cassette.



QUALITY
COMMITMENT

Our guarantee is simple:

If our products don't operate to specification, we replace them free of charge. Named the choice manufacturer seven of the past eight years and "Copier Manufacturer of the Year" three years straight, our fully-trained and certified, employee family is as knowledgeable as our copiers are dependable. You can count on Toshiba to deliver excellence in all we do. This is our quality commitment to you.



TOSHIBA



The Toshiba e-STUDIO170F is a hardworking facsimile system that helps make small and medium sized workgroups more productive. This multifunction unit can fax, print, copy and scan—faxing at an impressive rate of 3 seconds per page and printing at 17 pages per minute. Small and compact, the e-STUDIO170F is the perfect solution where space is limited.

- e-STUDIO170F** - 17 PPM Laser Fax Machine, 33.6 Kbps (110V)
- e-STUDIO170F220V** - 17 PPM Laser Fax Machine, 33.6 Kbps (220V)
- MY1025** - 500-Sheet Cassette
- GJ1110** - Handset
- OD170F** - Drum Unit
- ZT170F** - Toner

FEATURES

Fax Features

- Super G3, 33.6 Kbps Modem Speed
- 17 PPM Print Speed
- 3 Seconds Per Page Transmission
- 3 Second Quick Scan
- JBIG Compression
- 128 Level Gray Scale

Dialing Features

- 38 Programmable One-Touch Keys
- 150 Abbreviated/Alphabet Dials
- 188 Location Autodialer
- Automatic Redial
- Chain Dial
- Group Dialing (50 Groups)
- Multi-Key (Up to 100 manually dialed locations plus autodialer locations)

Transmission Features

- Auto/Manual Contrast Control
- Delayed Transmission (Up to 31 days)
- Direct Send Transmission
- Error Correction Mode (ECM)
- ITU-T Relay Transmission
- ITU Sub-Address Transmission
- Manual Broadcast
- Memory Transmission
- Multi-Location/Broadcast Transmission
- Polling (Simple, Secure, Delayed, Multi-Address)
- Priority Transmission (Up to 24 Hours)
- Recovery Transmission
- Reservation Transmission
- Smart Batching

Reception Features

- Automatic Legal to Letter Reduction
- FAX/TAD Auto Switch
- TEL/FAX Auto Switch
- Memory Reception
- Secure Reception
- Memory Features**
 - 7 MB Memory (Approximately 700 pages)*
 - Memory Backup (1 Hour)
 - Memory Release
 - Memory Overflow Protection
 - Multi-Memory Access

Multifunction Features

- Optional PC Faxing
- Single or Multi Copy (Up to 99 sequential)
- TWIN Scanning
- 600 dpi Windows® Printing
- Convenience Copy
- Compact Footprint
- Device Setup

Management Features

- Account Codes
- Department Codes (50)
- Confirmation Reports (With reduced image of 1st page)
- Power Save Mode
- Remote Terminal Identification (Display/Print)

Paper Handling

- 40-Sheet Automatic Document Feeder
- Collated Printing
- Letter or Legal Sheet Output Capabilities
- Single Sheet Bypass
- 250-Sheet Paper Cassette

SPECIFICATIONS

Useable Circuits

- Compatibility**
- Modem Speed (Kbps)**
- Data Compression**
- Transmission Speed**
- Page Memory**
- Memory Backup**
- Fax Resolution**

Public Switch Telephone Network (PSTN)

ITU-T Group 3, Super G3, ECM
33.6/28.8/14.4/9.6/7.2/4.8/2.4 Kbps
MH/MR/MMR/JBIG
Approx. 3 Seconds Per Page* (ECM)
7 MB (Approx. 700 pages)*

1 Hour
Standard Mode: 203 pels/in. x 98 lines/in.
(8 pels/mm x 3.85 pels/mm)
Fine Mode: 203 pels/in. x 196 lines/in.
(8 pels/mm x 7.7 pels/mm)
Ultra Fine Mode: 406 pels/in. x 391 lines/in.
(16 pels/mm x 15.4 pels/mm)

- Scanning Method**
- Gray Scale**
- Automatic Document Feeder**
- Scanning Speed**
- Effective Scanning Width**
- Contrast Control**

Contact Image Sensor (CIS)
128 Levels
40 Sheets

- Printing Method**
- Print Speed**
- Printing Resolution**
- Paper Supply**

3 Seconds Per Page Quick Scan*
Up to 8.4" (214 mm)
Automatic and 3 Step Selectable (Normal/Darker/Lighter)
Monochrome Laser
17 PPM
Print/Copy: 600 x 600 dpi
Standard: 250 Cut Sheet Plain Paper (Letter/Legal)
Optional: 500 Sheets (Letter)
Letter or Legal
150 Sheets

- Recording Paper Size**
- Receiving Paper**
- Output Tray**
- Connections**

RJ11 Telephone Jack
USB 2.0 Interface (Printing/Scanning)
Windows® 98 SE, 2000, Me, XP, Server 2003
110 VAC, 50/60 Hz
21.3"(W) x 19.7"(D) x 23.6"(H)
541mm x 500mm x 599mm
35.3 lbs. (16 kg)

- Operating Systems**
- Power Requirements**
- Dimensions**

Weight

* ITU Testchart #1, Standard Resolution.

Corporate Office: 2 Musick, Irvine, California 92618-1631

East Coast: 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054
Tel: 973/316-2700 Fax: 973/263-2393

Midwest: 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631
Tel: 773/380-6000 Fax: 773/380-8077

South: 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024
Tel: 770/209-8540 Fax: 770/209-8556

West Coast: 142 Technology, Suite 150, Irvine, California 92618
Tel: 949/462-6262 Fax: 949/462-2700

Web Site: www.copiers.toshiba.com or www.fax.toshiba.com

© 2005 Toshiba America Business Solutions, Inc., Electronic Imaging Division
e-STUDIO170F Brochure/Inv. Code ES170F1

Designs and specifications subject to change without notice. Actual specifications based on engine design and may vary according to usage and environment. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Driver and connectivity feature support varies by client/network operating system. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability.

AUTHORIZED TOSHIBA DEALER

