



The Multifunction Fax That's Big on Efficiency and Small on Space.

e-STUDIO50F

TOSHIBA
Don't copy. Lead.

e-STUDIO50F

Digital Laser Fax



The exceptionally productive e-STUDIO50F is an outstanding multifunction fax and laser printer that copies, faxes, scans and manages your documents...all from a very small 14" x 14.3" space. It offers crisp 600 dpi Windows® printing, a 100 location Autodialer, 60-page memory, convenience copying, and TWAIN scanning. It does everything you want at a price affordable enough for a single executive, yet efficient enough for a busy workgroup.

Products and Options List

Part Number	Description
e-STUDIO50F	5 PPM Laser Fax Machine, 33.6 Kbps - 110V
e-STUDIO50F 220V	5 PPM Laser Fax Machine, 33.6 Kbps - 220V
GJ1100	Handset, e-STUDIO50F
PU500F	Drum Unit, e-STUDIO50F
ZT500F	6K Yield Replacement Toner, e-STUDIO50F
ZT500FA	3K Yield Replacement Toner, e-STUDIO50F

FEATURES

Outstanding Performance

- Super G3, 33.6 Kbps Modem
- 3 Seconds Per Page Fax Transmission
- 5 PPM Print Speed

Exceptional Productivity

- Automatic Redial
- 18 One Touch Keys
- 100 Location Autodialer
- 1 MB Memory

Amazing Flexibility

- Standard Multifunction Features
 - Fax and PC Faxing
 - TWAIN Scanning
 - Scan-to-Email with Document Manager
 - 600 dpi Windows® Printing
 - Convenience Copy
- Compact Footprint

Easy to Use

- Convenient Document Management Software
- Dual Component, User Replaceable Supplies

SPECIFICATIONS

Compatibility

Modem Speed (Kbps)

ITU-T Group 3, ECM
33.6 / 31.2 / 28.8 / 26.4 / 24.0 / 21.6 / 19.2
16.8 / 14.4 / 12.0 / 9.6 / 7.2 / 4.8 / 2.4 Kbps

Data Compression

MH / MR / MMR

Transmission Speed

Approx. 3 Seconds Per Page

Page Memory

1 MB (Approx. 60 Pages)

Scanning Resolution (Fax)

Standard Mode: 203 pels/in. x 98 lines/in.
8 pels/mm x 3.85 pels/mm
Fine Mode: 203 pels/in. x 196 lines/in.
8 pels/mm x 7.7 pels/mm
Super Fine Mode: 203 pels/in. x 391 lines/in.
8 pels/mm x 15.4 pels/mm

Scanning Method

Contact Image Sensor (CIS)

Gray Scale

64 Levels

Automatic Document Feeder

Approx. 20 Sheets

Effective Scanning Width

8.35 in. (212 mm)

Printing Method

Monochrome Laser

Print Speed

5 PPM

Printing Resolution

Fax/Copy: 406 x 391 dpi
Printer: 600 x 600 dpi

Paper Supply

Recording Paper Size

Approx. 150 Cut Sheet Plain Paper

Connections

Letter or Legal
RJ11 Telephone Jack
Parallel Interface (Printing/Scanning)

Supplies

Ships with 1K Yield Starter Cartridge
3K or 6K Yield Replacement Cartridges

Operating Systems

Windows® 98
Windows® NT 4.0
Windows® 2000
Windows® Me
Windows® XP

Power Requirements

Power Consumption

108-132 VAC, 47-63 Hz Single Phase
Standby (Sleep Mode) Approx. 0.7 Wh
(Energy Saver: On) Approx. 5.5 Wh
(Energy Saver: Off) Approx. 17 Wh
Transmission Approx. 17 W
Reception Approx. 450 W
Copy Approx. 450 W
Maximum Approx. 470 W

Dimensions

14.0" (W) x 14.3" (D) x 8.7" (H)
355 mm x 364 mm x 220 mm

Weight

16.1 Lb. (7.3 kg)

Corporate Office: 2 Musick, Irvine, California 92618-1631

East Coast: 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054
Tel: 973/316-2700 Fax: 973/263-2393

Midwest: 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631
Tel: 773/380-6000 Fax: 773/380-8077

South: 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024
Tel: 770/209-8540 Fax: 770/209-8556

West Coast: 142 Technology, Suite 150, Irvine, California 92618
Tel: 949/462-6262 Fax: 949/462-2700

Web Site: www.fax.toshiba.com or www.copiers.toshiba.com

© 2003 Toshiba America Business Solutions, Inc., Electronic Imaging Division
e-STUDIO50F Specification Sheet/Inv. Code ES50F01

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 4% coverage, letter-size page.

AUTHORIZED TOSHIBA DEALER

TOSHIBA
COPY ■ FAX ■ PRINT