

- > **Up to 30 PPM**
- > **Black & White MFP**
- > **Sml/Med Workgroup**
- > **Copy, Print, Scan, Fax**
- > **Secure MFP**
- > **Eco Friendly**

e-STUDIO205L/255/305



Introducing the finest business decision you can make.

At a time when some businesses are making tough decisions, Toshiba offers a simple one—the e-STUDIO205L/255/305 Series. It streamlines operations and boosts productivity to an all-new level. Every document that's printed is crisp and clear, thanks to Toshiba's own ultrafine toner. When it comes to describing every other aspect of this innovative line of products, ultrafine may be precisely the right word.

User-friendly and fiercely competitive

Ease of use has been given top priority with the e-STUDIO205L/255/305 Series. Small and medium size workgroups can make fast work of complicated jobs. For greater efficiency, these black and white multifunction devices are intuitive as well as competitive. The graphical user interface is simple to use. Frequently performed tasks can be pre-programmed for swift execution, every time. The 8.5" WVGA color control panel makes multiple functions easy to navigate with its large icons and buttons. Its extended, tilt-adjustable range can be adapted for each user and meets the Section 508 disability act. In addition, new templates and "My Menu" functions make operation easier still.

Single footprint, multiple functions

This new line of small, compact MFPs is designed to occupy less space while handling more work. Network printing and color scanning come standard. More options can be added, such as walk-up faxing, PC-LAN faxing, and advanced scanning to MS Word, MS Excel & Searchable PDF. Choose from copy and print speeds of 20, 25, and 30 pages per minute. Also, several functions can be performed simultaneously—print and fax, print and scan, copy and scan, you name it.



- > 3,200-Sheet Capacity
- > 30,000 Toner Yield
- > USB Direct Scan & Print
- > Exceptionally Crisp Output
- > High Speed Auto Duplex
- > Standard Network Printing
- > Add Paper "On the Fly"





Give office productivity a raise.

Why make cutbacks when you can improve productivity instead? After all, it's the small things that make a big difference, like the e-STUDIO205L/255/305 Series. Designed into this small footprint are a host of functions: print, fax, copy, scan, store, send, save, duplex, sort, stack, secure, file, browse, and even sleep. If you need it, it's in there.

secureMFP

- > Secures Print Output
- > Secures Data
- > Creates Secure PDF
- > Controlled Access



Feel secure in your decision

Of all the functions these devices can perform, self-protection may be the most impressive. You can never be too safe with strategic data; hence, Toshiba works hard to make sure it stays right where it belongs. Password data is encoded instead of sent in plain text across the network. A hard drive encryption feature is standard, with virtually unbreakable Advanced Encryption Standard (AES) code like that used by the U.S. Department of Defense. In case that's not enough, opt for a data overwrite enabler and complete LDAP authentication.

Handle color with black and white

Now you can manage color documents without investing in a full color MFP, thanks to the e-STUDIO205L/255/305 Series. It scans in color to capture, manage and store color images in their original format and full-color glory. Also, a unique Color Document Mode makes clear, readable monochrome copies of color originals.

Let's speak volumes

You'll be surprised at how much these small, compact MFPs can produce, and how efficiently they do it. Paper capabilities include a standard Auto Duplex Unit along with two 550-sheet drawers and a 100-sheet bypass tray. Need more? Opt for a 100-sheet RADF, additional paper drawers, and a large capacity feeder. In total, you have a 3,200-sheet capacity, if need be. Whether your document processing requirements are average, extra large or both, depending on the day, Toshiba has the solution.

- > Color Scanning
- > Compact Footprint
- > Improved Security
- > TopAccess Control
- > e-BRIDGE Technology



Get your workflow flowing.

All businesses are looking to improve productivity these days. Toshiba has created the ideal method to achieve just that with the e-STUDIO205L/255/305. Feature for feature, function for function, square foot for square foot, no other line of multifunction devices can compare.

Conserve energy while boosting productivity

Creating environmentally responsible products is among our greatest technological achievements. The e-STUDIO205L/255/305 Series is Energy Star, ISO-14001, ISO-9001, and RoHS compliant—not to mention lead-free, halogen-free, and chromium-free. Various user features offer energy savings, like our Super Sleep Mode which uses just one watt of power. In addition, product manuals are provided in electronic form to reduce waste. Our involvement in conservation programs includes Close the Loop, a zero waste to landfill initiative. Your local Toshiba representative can provide further details on these programs.



That's not all

There are a host of other features and functions that set this line of multifunction devices apart. Like, for instance, Original Outside Erase which removes the surrounding dark or black area of a copy or scan if the platen cover or RADF is open. "Paper on the fly" allows paper to be added during operation so work can continue uninterrupted. Omit Blank Page identifies and omits blank pages in the original document when it's scanned. These are just a few of the advanced features and benefits that can put less work and more flow into your workflow.

The Managed Print Experts


At Toshiba, we've moved far beyond the box. Our people bring innovative, real-world solutions to all your print management needs. We'll help you cut costs, secure your documents and reduce your environmental footprint. And if there's one thing every business and our planet can use right now, it's managing to do more with less.

See for yourself. Call or visit your nearest Toshiba dealer. Let us show you how to gain a competitive edge, or an unfair advantage—whichever way you care to look at it.





- > Improved Ease of Use
- > Super G3 Fax
- > Bluetooth Wireless
- > Saddle Stitch Booklets
- > Stapling & Hole Punch





- > Black & White MFP
- > Up to 30 PPM
- > Sml/Med Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly

Specifications

Copying Process/Type	IEPM (Dry Process)/Laser Technology
Original Reading Method	CCD Line Sensor
Copy/Print Resolution	2400 x 600 dpi (with Smoothing)
Copy/Print Speed	20 / 25 / 30 ppm
Scanning	Color Scanning
Warm-Up Time	Appx. 20 Seconds
First Copy Time	4.7 Seconds
Duty Cycle	80K / 100K / 120K
Multiple Copying	Up to 999 Copies
Standard Paper Supply	2 x 550-Sheet, 100-Sheet Stack Feed Bypass
Maximum Paper Supply	Up to 3,200 Sheets
Acceptable Paper Size	Cassette: Statement-R to Ledger (17-28 lbs.); Bypass: Statement-R to Ledger (17-110 lbs.); LCF: Letter (17-28 lbs.)
Special Paper	Bypass: Envelope, Tab Sheet
Memory	1GB RAM, 60 GB HDD
Reduction/Enlargement	25% to 400%
Bypass Tray	100-Sheet Stack Feed Bypass
Control Panel	8.5" Wide VGA Color Touch-Screen
Dimensions	Appx. 23" x 23" x 30" (W x D x H)
Weight	Appx. 125 lbs.
Power Supply	115 Volts; 15 Amps
Power Consumption	Maximum 1.5kW
PM Cycle	80K / 100K / 120K
Black Toner Yield	30K Impressions
Drum Type/Yield	Organic Photoconductor; 80K / 100K / 120K
Developer Yield	80K / 100K / 120K

Print (Standard)

Print Speed	20 / 25 / 30 ppm
PDL Support	PCL6, PostScript3, XPS
Operating Systems	Windows 2000/XP/2003/Vista/2008; Mac X OS10.2.4/10.3 10.4/10.5; UNIX, Linux, CUPS
Protocol Support	IPX/SPX, TCP/IP (IPv4/IPv6), EtherTalk, AppleTalk PAP, LPR/LPD, IPP w/Authentication, Port 9100 Bluetooth, SMB, Netware
Drivers	Windows 2000/XP/2003/Vista/2008; Mac X OS 10.2.4/10.3 10.4/10.5 (OS 10.4 PPD), UNIX, Linux, AS/400, SAP R/3
Connectivity	Ethernet 10/100BaseT, USB 2.0, 802.11b/g Wireless LAN, Bluetooth (HCRP)
Device Management Certification	TopAccess WHQL, Novell, HPOS (Dazell), Vista Premium

Scan (Standard)

Scan Speed	57spm LT-Size@300dpi (B&W)/43spm LT-Size@300dpi (Color)
Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
File Format	TIFF, PDF, Slim PDF, JPEG, XPS
Authentication	MS Word, MS Excel, Searchable PDF w/ Adv. Scanning option LDAP, SMTP, Windows Server Domain

E-Filing (Standard)

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box; 200 Private User Boxes
Capacity of Boxes	100 Folder per Box; 400 Documents per Folder; 1000 Pages per Documents

Facsimile Option

Compatibility	Super G3, G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Appx. 3 Seconds per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	Transmission 500MB (HDD); Reception 200MB (HDD); Backup Permanent (HDD)
Memory Transmission	100 Jobs; 1,000 Destinations Max; 400 Destinations/Job
Scan Speed	0.7 Seconds per Page; 50 Scans per Minute
Other Fax Functions	Internet Fax; Network Fax

Accessories (Options)

Input Options	
100-Sheet RADF	MR3021
Platen Cover	KA1640PC
Additional Paper Options	
550-Sheet Paper Feed Pedestal	KD1025
2,000-Sheet Large Capacity Feeder	KD1026
550-Sheet Paper Feed Unit	MY1033
Finishing Options	
Job Separator	MJ5004
Offset Tray	MJ5005
Work Tray	KK4550
Bridge Kit for Finisher	KN2520
50-Sheet Staple Hanging Finisher	MJ1031
Saddle-Stitch Finisher	MJ1025
2 or 3 Hole Punch Unit for MJ1025	MJ6005
Connectivity/Security Options	
Fax Kit	GD1250
2nd Line Fax	GD1260
Data Overwrite Kit	GP1070
IPSec Enabler	GP1080
Wireless LAN Adapter	GN1050
Bluetooth Module	GN2010
Antenna	GN3010
Meta Scan Enabler	GS1010
External Interface Enabler	GS1020
Advanced Scanning	GB1280T
Miscellaneous Options	
Smart Card HID	KP2004
Smart Card Mifare	KP2005
Accessible Arm Handle	KK2550
Harness Kit for Coin Controller	GQ1180



Corporate Office	2 Musick, Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-3136-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	142 Technology, Suite 150, Irvine, CA 92618 Tel: 949-462-6262
Web Site	www.copiers.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.