

Productivity.
Mobility.
Reliability.
And Pure Sensibility.

eSTUDIO™ 500P



50



Workgroup



Black & White

TOSHIBA
Don't copy. Lead.

e-STUDIO™ 500P

Digital Laser Printer

The e-STUDIO500P is the high-quality printer designed to meet the needs of larger workgroups. 2400 dpi image quality is delivered at an impressive 50 pages per minute. Add a variety of options for an excellent stand alone printer or complement to other e-STUDIO MFP solutions.



A strong 514 MHz processor helps produce a fast 50 PPM.

A standard USB port allows for direct USB printing.

The e-STUDIO500P offers an input capacity of up to 4,100 sheets.

FEATURES

Outstanding Performance

- High-Speed 50 Pages Per Minute
- Fast 8.5 Second First Print Out Time
- Robust 514 MHz Processor
- 128 MB Memory/640 MB Max
- True 1200 x 1200 dpi Resolution

Amazing Productivity

- Up to 250K Pages Per Month
- PostScript™ 3 and PCL6™ Support

Flexible Connectivity

- Standard 10/100BaseT Connection
- Standard Parallel Port
- Standard USB 2.0 Connection
- Optional 802.11g Wireless Adapter
- Direct USB Printing

Tremendous Paper Handling

- Standard 500-Sheet Paper Capacity
- Standard 100-Sheet Bypass
- Input Option Capacity up to 4,100 Sheets
- Up To Legal Paper Size
- Optional Duplex
- Envelope Printing
10 Standard
85 Max. w/Optional Envelope Tray

Easy to Use

- Advanced Management Software (when networked)
- Supports All Popular Operating Systems
- User Replaceable Supplies

OPTIONS

e-STUDIO500P	50 PPM Monochrome Laser 110V
1010042	802.11g Wireless Adapter
20G0890	500-Sheet Drawer
20G0892	2,000-Sheet Drawer
20G0888	Duplex Unit
20G0891	Envelope Tray
13N1523	128 MB DDR-DRAM Module
13N1526	512 MB DDR-DRAM Module
24B0351	32K Yield Toner Cartridge (Regular)
24B0356	32K Yield Toner Cartridge (Use and Return)

SPECIFICATIONS

Engine Technology	Monochrome Laser
Print Speed	Up to 50 Pages Per Minute 8.5 Second First Print Out Time (FPOT)
Print Quality	2400 dpi Image Quality 1200 x 1200 dpi Resolution 600 x 600 dpi Resolution
Processor	514 MHz
Memory	128 MB - Standard 640 MB - Maximum
Connectivity (Standard)	10/100BaseT Port USB Port Parallel Port
Connectivity (Options)	External 802.11g Wireless Adapter
Compatibility	PostScript™ 3 Emulation PCL6™ Emulation
Paper Handling	Input Standard/Maximum – 600/4,100 Sheets Output Standard/Maximum – 500/500 Sheets
Media Sizes	Letter, Legal, A4, A5, JIS B5, Executive, Statement, and Universal (2.75" x 5" to 8.5" x 14") Envelopes: DL, C5, B5, 7.75, 9, 10
Media Types	Plain Paper, Envelopes, Card Stock, Transparencies, Paper Labels
Media Weights	Up to 110 lb. Index – Standard Integrated Drawer Up to 90 lb. Index – Bypass and Optional 500-Sheet Drawer Up to 28 lb. Bond – 2,000-Sheet Drawer
Supplies	Ships with 21K Yield Starter Cartridge 32K Yield Replacement Cartridge – Regular and Prebate Available
Operating Systems	Windows® 2000, Me, Windows® NT 4.0, XP, Server 2003, Macintosh® 9.x, 10.2 or higher, Novell® NetWare 3.x, 4.x, 5.x, 6.x
Size	20.6" (L) x 17.2" (W) x 16" (H) 523mm x 436mm x 406mm
Weight	51 lb. (23.1 kg)
Acoustics	55 dBA Printing 30 dBA Idle
Maximum Monthly Volume	Up to 250,000 Pages Per Month

Corporate Office: 2 Musick, Irvine, California 92618-1631

East Coast: 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054
Tel: 973/316-2700 Fax: 973/263-2393

Midwest: 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631
Tel: 773/380-6000 Fax: 773/380-8077

South: 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024
Tel: 770/209-8540 Fax: 770/209-8556

West Coast: 142 Technology, Suite 150, Irvine, California 92618
Tel: 949/462-6262 Fax: 949/462-2700

Web Site: www.copiers.toshiba.com or www.fax.toshiba.com

© 2006 Toshiba America Business Solutions, Inc., Electronic Imaging Division
e-STUDIO500P Specification Sheet/Inv. Code ES500P2

Designs and specifications subject to change without notice. Actual specifications based on engine design and may vary according to usage and environment. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Toner yields are estimates, based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability.

AUTHORIZED TOSHIBA DEALER

TOSHIBA
COPY ■ FAX ■ PRINT