

The *compact* printer designed for *large* jobs.



**e-STUDIO™ 350P**



35



Workgroup



Black & White

**TOSHIBA**  
Leading Innovation >>>

# e-STUDIO™ 350P

## SPECIFICATIONS

The Toshiba e-STUDIO350P is a compact black & white printer designed for individuals and small workgroups. Fast, powerful and reliable, this hard-working printer delivers sharp 1200 x 1200 dpi at 35 pages per minute with a first page out time of just 6.5 seconds.



High speed output of 35 Pages Per Minute



First page out time of just 6.5 seconds



User-friendly 2 line display makes operation easy

## SPECIFICATIONS

<b>Engine Technology</b>	Monochrome Laser
<b>Print Speed</b>	Up to 35 Pages Per Minute 6.5 Second First Print Out Time (FPOT)
<b>Print Quality</b>	2400 Image Quality 1200 x 1200 dpi Resolution 600 x 600 dpi Resolution
<b>Memory</b>	32 MB - Standard 160 MB - Maximum
<b>Connectivity</b>	(Standard) Parallel, USB, 10/100BaseTX Ethernet
<b>Compatibility</b>	PostScript™3 Emulation PCL6™Emulation
<b>Paper Handling</b>	Input Standard/Maximum – 250/800 Sheets Output Standard/Maximum – 150/150 Sheets
<b>Media Sizes</b>	Letter, Legal, A4, A5, JIS B5, Executive, Folio and Statement - Standard Tray and Optional Drawer Universal (3" x 5" to 8.5" x 14") – Bypass Envelopes: DL, C5, B5, 7/8, 9, 10 – Bypass
<b>Media Types</b>	Plain Paper, Transparencies, Paper Labels – Standard Tray, Bypass and Optional Drawer Card Stock - Bypass
<b>Media Weights</b>	Up to 90 lb. Index – Bypass 16 – 24 lb Bond – Standard and Second Tray For cardstock up to 90 lb Index, use rear exit door for straight through paper path
<b>Supplies</b>	Ships with 3K Yield Starter Toner Cartridge Ships with 30K Photoconductor 9K Yield Replacement Cartridge – Regular and Use and Return available
<b>Operating Systems</b>	Windows® 95/98/2000/NT/Me/XP, Vista, Mac® 9.x, 10.2 and up
<b>Size</b>	14.1" (L) x 15.6" (W) x 10.2" (H) 359 mm x 396 mm x 259 mm
<b>Weight</b>	25 lb. (11.37 kg)
<b>Acoustics</b>	52 dBA Printing Inaudible Idle
<b>Maximum Monthly Volume</b>	Up to 35,000 Pages Per Month

## FEATURES

<b>Exceptional Performance</b>	Quick 35 Pages Per Minute Fast 6.5 Sec. First Print Out Time Superior 2400 Image Quality True 1200 x 1200 dpi resolution
<b>Outstanding Productivity</b>	Up to 35K Pages Per Month Ultra-Compact Footprint PostScript™ 3 and PCL6™ Support
<b>Flexible Connectivity</b>	Standard Parallel Port Standard USB Port Standard 10/100BaseTX Ethernet Port
<b>Excellent Paper Handling</b>	Standard 250-Sheet Paper Capacity Optional 550-Sheet Drawer Letter/Legal Paper Size Single Sheet Bypass Envelope Printing
<b>Easy to Use</b>	Supports All Popular Operating Systems Dual Component, User Replaceable Supplies

## SUPPLIES

<b>24B2048</b>	Black Toner, Use and Return, 9K Yield
<b>24B2049</b>	Black Toner, Regular, 9K Yield
<b>24B2050</b>	Photoconductor, Single Unit, 30K Yield

## ACCESSORIES

<b>14T0145</b>	Wireless Print Server
<b>28S0803</b>	550-Sheet Drawer
<b>5K00016</b>	32 MB Memory Expansion
<b>5K00017</b>	64 MB Memory Expansion
<b>5K00119</b>	128 MB Memory Expansion

**Corporate Office:** 2 Musick, Irvine, California 92618-1631  
**East Coast:** 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054  
Tel: 973/316-2700 Fax: 973/263-2393

**Midwest:** 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631  
Tel: 773/380-6000 Fax: 773/380-8077

**South:** 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024  
Tel: 770/209-8540 Fax: 770/209-8556

**West Coast:** 142 Technology, Suite 150, Irvine, California 92618  
Tel: 949/462-6262 Fax: 949/462-2700

**Web Site:** www.copiers.toshiba.com or www.fax.toshiba.com

© 2007 Toshiba America Business Solutions, Inc., Electronic Imaging Division  
e-STUDIO350P Spec/Inv. Code ES350P2

Designs and specifications subject to change without notice. Actual specifications based on engine design and may vary according to usage and environment. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Toner yields are estimates, based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability.

AUTHORIZED TOSHIBA DEALER

**TOSHIBA**  
Leading Innovation >>>