

e-STUDIO™ 281c The Economy of Black and White

– and Color on Demand.



TOSHIBA
Don't copy. Lead.

A Full Spectrum

of Economy and Features



If you're looking for the economy of black & white but want the capabilities of color, look no further than the Toshiba e-STUDIO281c. This multifunction device gives your documents the advantage of color while

offering required features such as copying, scanning, printing, faxing, and finishing. Best of all, independent color and black & white development systems provide a cost per copy for black & white printing that's consistent with the economy found in most monochrome-only multifunction devices.

The color-enhanced e-STUDIO281c multifunction device offers high productivity and high quality with the convenience

of color — for all your printing, copying, and scanning needs.


It delivers superb performance and productivity with next-generation e-BRIDGE technology, fast 600 MHz processor, 80 GB hard disk drive, and enhanced duplex productivity.

The e-STUDIO281c produces crisp, clear black & white output at a rate of 28 pages per minute and attention-grabbing color pages at 11 pages per minute. You're in control of the color and save time, money, and effort while increasing the impact and effectiveness of your documents and presentations.

Add the impact of color to make your presentations more dynamic. ▶



Rich functionality with a low cost for black & white printing that is consistent with the cost per copy on monochrome multifunction devices. ▶





▲
Toshiba's e-STUDIO281c
transforms paper documents
and electronic files into
printed pages, presentations,
Emails, and faxes.





The e-STUDIO281c is built to perform in any mode. Use the device as a network printer, scanner, fax machine, and of course, as a copier — while avoiding the cost and maintenance associated with dedicated equipment. Keep the highlights colorful while enjoying the speed, clarity, and economy of black & white for everyday jobs.

The e-STUDIO281c multifunction device includes net-ready single board architecture that incorporates Toshiba's next-generation e-BRIDGE technology. This unified approach allows you to add functionality as you need it — just plug and print. Using e-FILING, you can distribute data to multiple destinations with a few easy steps. Other features include Scan-to-Email, Internet Faxing, and TopAccess — a remote device management utility with a common interface across all Toshiba multifunction products. And to perform all functions with greater speed, the e-STUDIO281c uses a lightning-fast 600 MHz processor.



Performance, Productivity, and Exceptional Quality

for All Your Printing, Copying, Scanning, and Faxing Needs-Plus the Added Convenience of Color



Set permissions for color printing and copying by department or individually to track and manage costs.

Tilting, wide-touch control panel is 508 compliant and increases visibility, making the device easier to use and access.

Professional document finishing includes stapling, hole punch, and saddle-stitch.

A trayless Automatic Duplexing Unit (ADU) handles two-sided originals quickly and easily to reduce paper costs.

With an innovative color revolver printing system, black & white and color originals can be easily mixed in the same job.

A high-yield black toner cartridge saves time and money by reducing the need for replacement.

A compact design with inner exit tray saves valuable space.





eCopy Ready

The e-STUDIO281c supports eCopy's ScanStation OP. This option enables you to seamlessly integrate the device with networked applications, including your company's Email system. This functionality gives you a low-cost, easy, and instantaneous distribution and management system for all your scanned documents. The eCopy feature helps extend how you use your e-STUDIO281c while maximizing existing investments in your corporate network infrastructure and applications.

User Management and Privacy

The e-STUDIO281c also offers improved department code functionality for more robust device management capabilities. When color restriction is enabled, department codes are only needed to make color copies and prints — there's no restriction on black & white copies. In addition, managers can track and restrict the use of color or black & white functionality according to department code, or

even an individual's password. Private print makes printing sensitive documents secure — even in a busy office.

Document files sent from a PC are held by the device until accessed via password.

Versatile, Powerful Output

The e-STUDIO281c gives you the power to create for any purpose. Use cover-weight paper, OHP sheets, and tab sheets — whatever suits your presentation needs. Finish a job professionally with automatic stapling, hole punch, saddle-stitch finishing, and magazine sort. Plus, you can record what works — the device stores specific copy, fax, scan, and finishing settings as easy-to-access templates — up to 12,060 of them.





Heightened Security

Along with productivity and performance, today's businesses are becoming more and more concerned about security. That's why we've included features to make the e-STUDIO281c even more secure. The data overwrite feature writes over the data after each job is processed to protect confidential information. In addition, an optional scrambler board encrypts hard drive data to secure stored documents. Furthermore, complete LDAP authentication provides an additional layer of security by controlling access to the device.

Demand Yours Today

The e-STUDIO281c is an advanced multifunction copier that adds color on demand without sacrificing the economy and speed of black & white. Buy just one device that matches your document reproduction needs along with advanced connectivity to work as a fax machine, network scanner, and Scan-to-Email device. For everyday office printing with the flexibility of color, the e-STUDIO281c is perfect for every business looking to improve communications economically.

COPY FEATURES

- Access Codes (1,000 Department / 10,000 User)
- Annotation (Date / Time Print)
- AMS / APS (RADF and Platen)
- Auto Job Start
- Auto Cassette Change
- Auto Trayless Duplex
- Auto Energy Saver
- Auto Sleep Mode
- Color Image Adjustments
- Cover Sheet
- Dual Page Copying
- Edge Erase
- e-FILING (Document Storage)
- Electronic Sort
- Energy Saver
- Image Shift
- Interrupt
- Job Templates
- Job Reservation (Scan Ahead)
- Magazine Sort (Booklet Making Mode)
- Mirror Image
- Negative / Positive
- Page Numbering
- Rotation Copy
- Sheet Insertion
- Weekly Timer
- X-Y Zoom
- 2-in-1, 4-in-1, 8-in-1 Duplex

PRINT FEATURES

- Cover Sheet
- DocMon – Document Monitor Utility
- Duplex Printing
- Hole Punch
- Magazine Sort
- Mixed Size Printing
- Private Print
- Proof Print
- Saddle-Stitch / Booklet Mode
- Scheduled Print
- Sheet Insertion
- Stapled Sets
- Store to e-FILING
- Watermark

SCAN FEATURES

- Color and B&W Scanning
- Scan-to-File
- Scan-to-e-FILING
- Scan-to-Email
- Scan-to-FTP
- TWAIN Compatible

FAX FEATURES (OPTIONAL)

- Address Book (1,000 Addresses)
- Automatic Redial
- Broadcasting (Max. 1,000 Destinations)
- Chain Dialing
- Delayed Transmission
- Direct Transmission
- Double Sided Scanning and Reception
- Dual Access
- Group Dialing (Max. 200 Groups / 400 Destinations / Group)
- Optional Second Line
- Network Faxing
- Polling
- Priority Transmission
- Public Mailbox (F-Code)
- Route Fax to Folder / Email / e-FILING
- TX / RX Reporting

DEVICE MANAGEMENT FEATURES

- TopAccess Device Management Utility
- Email Notification for Service Calls
- Email or Fax Notification for Counters and Preventative Maintenance
- Automatic Supply Ordering
- Department Code Enforcement
- Access Limitations for Color and B&W

SPECIFICATIONS	
Copying / Printing Process	Indirect Electrostatic Photographic Method
Copy System	Color Laser, Toshiba Revolver B&W/Color Printing System
Original Scanning Method	CCD Line Sensor (4-Lines)
Copy / Print Resolution	600 x 600 dpi B&W: 2,400 x 600 dpi with Smoothing Color: 1,200 x 600 dpi with Optional Expansion Memory
Copy / Print Speed	28 PPM B&W / 11 PPM Color
Warm Up Time	Approximately 40 Seconds
First Copy Out Time	B&W: 6.8 Seconds Color: 16.2 Seconds
Duty Cycle	100,000 Copies
Multiple Copying	Up to 999 Copies
Paper Supply	Up to 3,700 Sheet Input Capacity Standard: 2 x 550 Sheet Cassettes (17-28 lbs.) Optional: 1 x 550 Sheet PPF, 1 x 550 Sheet Cassette, 1 x 2,500 Sheet LCF
Bypass	Stack Feed "Smart" Bypass (100 Sheets)
Acceptable Paper Size	Cassette: Statement-R to Ledger (17-28 lbs.) Bypass: Statement-R to 12" x 18" (17-110 lbs.) LCF: Letter (17-28 lbs.)
Duplex	Standard Trayless Automatic Duplex Unit
Maximum Original Size	Ledger
Standard Memory	384 MB, 80+ GB HDD
Optional Memory	Up to 768 MB
Color Mode	Automatic Color Selection, Full Color Mode, Black Mode, Twin Color
Color Image Adjustments	Color Balance, RGB, Sharpness, Background, One Touch
Reduction Enlargement	25% - 400%
Dimensions	30"H x 26"W x 29"D
Weight	247 lbs.
PM Cycle	100,000
Toner Control Method	Automatically Controlled; Toner Empty Detection
Drum Type	Organic Photoconductor
Black Toner Yield	27,000
Color Toner Yield	10,000 Per Color (C,M,Y)
Power Supply	115V, 15 Amps
Power Consumption	Maximum 1.5 kW
PRINT	
Processor	600 MHz (Shared for All Imaging Functions)
PDL Support	PCL5c, PCL6, PostScript 3
Operating Systems	Netware 4.x, 5.x, 6.x, Windows Me/2000/XP, Windows NT 4.0, Windows Server 2003, Citrix MetaFrame, Macintosh, Linux, UNIX
Protocol Support	IPX/SPX, TCP/IP, EtherTalk, AppleTalk, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
Drivers	Windows Me, 2000, Server 2003, XP, NT 4.0 Macintosh OS 8.6, 9.x, 10.1/10.2/10.3 (with PPD), UNIX, AS400 via iData and Port 9100, SAP R/3
Connectivity	10BaseT/100BaseTX Ethernet, USB, IEEE 1284, IEEE 802.11b/g Wireless LAN, Bluetooth (HCRP)
Device Management	TopAccess
Certification	WHQL, Novell



Corporate Office: 2 Musick, Irvine, CA 92618-1631
East Coast: 959 Route 46 East, 5th Floor, Parsippany, NJ 07054
 Tel: 973/316-2700 Fax: 973/263-2393
Midwest: 8770 W. Bryn Mawr Ave., Suite 700, Chicago IL 60631
 Tel: 773/380-6000 Fax: 773/380-8077
South: 4855 Peachtree Industrial Blvd., Suite 210, Norcross, GA 30092-3024
 Tel: 770/209-8540 Fax: 770/209-8556
West Coast: 142 Technology, Suite 150, Irvine, CA 92618
 Tel: 949/462-6262 Fax: 949/462-2700
Web Site: www.copiers.toshiba.com or www.fax.toshiba.com.
 © 2005 Toshiba America Business Solutions, Inc., Electronic Imaging Division
 e-STUDIO281c Brochure/Inv. Code ES281C1

SCAN

Scan Resolution	B&W: 600, 400, 300, 200, 150, 100 dpi Grayscale: 600*, 400, 300, 200, 150, 100 dpi Color/ACS: 600*, 400*, 300, 200, 150, 100 dpi *Optional Expansion Memory Required
Scan Speed	B&W: Up to 50 SPM Grayscale: Up to 45 SPM Color: Up to 40 SPM
File Format	TIFF Single/Multipage, PDF, JPEG
Authentication	LDAP, SMTP

e-FILING

Operation Method	Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder, 200 Pages Per Document
File Format	TIFF-MMR, TIFF-S, PDF, JPEG

FACSIMILE

Compatibility	Super G3
Modem Speed	33.6 Kbps
Compression Method	MH, MR, MMR, JBIG
Transmission Speed	Approximately 3 Seconds Per Page
Fax Memory	500 MB Transmission, 120 MB Reception, 80+ GB HDD Backup
Memory Transmission	100 Jobs, 1,000 Destinations Max, 400 Destinations/Job
Scan Speed	0.7 Seconds Per Page, 50 SPM

OPTIONS

MR3018 Reversing Auto Document Feeder (RADF)	Simplex Originals (13-55 lbs.) Duplex Originals (13-42 lbs.)
KD1011 Paper Feed Pedestal (PFP)	550-Sheet Pedestal, Statement-R to Ledger (17-28 lbs.)
MY1021 Cassette Module	550-Sheet Drawer, Statement-R to Ledger (17-28 lbs.)
KD1012 Large Capacity Feeder (LCF)	2,500-Sheet Drawer, Letter (17-28 lbs.), Stacks Side-By-Side (2 x 1,250)
MJ1022 Single-Position Hanging Finisher	2 Tray, Hanging Design, Tray 1 Stack Capacity: 200 Sheets (Lt), Tray 2 Stack Capacity: 700 Sheets (Lt), Staple Capacity: 30 Sheets (Lt/Lt-R, 20 lbs.)
MJ1023 Multi-Position Stapling Finisher	2 Tray, Console Design, Tray 1 Stack Capacity: 1,000 Sheets (Lt), Tray 2 Stack Capacity: 1,000 Sheets (Lt), Staple Capacity: 50 Sheets (Lt/Lt-R, 20 lbs.)
MJ1024 Multi-Position Stapling Finisher with Saddle-Stitch	2 Tray + Saddle-Stitch Tray, Console Design, Tray 1 Stack Capacity: 1,000 Sheets (Lt), Tray 2 Stack Capacity: 1,000 Sheets (Lt), Staple Capacity: 50 Sheets (Lt/Lt-R, 20 lbs.)
MJ6004 Hole Punch Unit	2 or 3 Hole Punch Capability
KN3511 Bridge Kit	Required with MJ1022, MJ1023, MJ1024
KA3511 Platen Cover	
KK3511 Work Tray	
GD1200 Fax Board	
GD1160 2nd Line Fax Board	
GN1040 802.11b/g Wireless LAN Adapter	
GN2010 Bluetooth Module	
GN3010 Wireless Antenna	
G01060 PCI Slot	
GF1140 Parallel Interface Kit	
GP1040 Scrambler Board	
GP1060 Data Overwrite Kit	
GQ1020 Coin Controller Wiring Harness	
GC1181 128 MB Memory Upgrade	
GC1230 512 MB Memory Upgrade	

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

