- > Up to 85 PPM
- > Black & White MFP
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly

E-STUDIO 555/655/755/855



The power to outperform.

Each year at Toshiba, we face the challenge of creating a series of MFPs (multifunction products) so exceptional, they even outperform our prior achievements. A daunting task, to be sure, but one to which we dedicate our time, talent, and ever-broadening vision. Which brings us to one of our most innovative accomplishments to date—the e-STUDIO555/655/755/855 Series. Large workgroups and departments can increase workflow dramatically, with a host of unique features that put high quality, high volume production at your fingertips.

Speed and precision

Begin with a first copy out time of less than 4 seconds, followed by a sleek production rate of 55, 65, 75, and 85 pages per minute, respectively. The sheer volume of work is impressive too, thanks to an internal 3,600-sheet base capacity (7,600 max), and monthly copy volumes of 460K, 515K, 540K, and 600K, respectively. Fast speeds and high volume output are accomplished without compromising image quality. In fact, our 8-bit scanner and revolutionary ultrafine toner give every single page an exceptionally crisp, professional look. If you aren't sure how much power and performance you need, your Toshiba representative can accurately determine which MFP will bring your workflow up to speed, and beyond.

Features and more features

One of the most highly lauded features is our scan-to and print-from USB flash drive capability. Other features are equally impressive, such as tab printing and copying that can be inserted within the document, heavy paper support up to 110 lb., a 100-sheet finisher and 4,000-sheet finisher capacity, industryleading monthly copy volumes and periodic maintenance intervals as well as an impressive toner yield at 62,400. Efficiency is also enhanced with Toshiba's innovative toner replacement feature that allows toner to be replaced "on the fly" without stopping or slowing operation.



> 3,600-Sheet Base

> 7,600-Sheet Max

> 62,400 Toner Yield

> USB Direct Scan & Print

> Exceptionally Crisp Output

> Tab Printing & Copying

> 2nd Line Fax Option

> 100-Sheet Finisher

> Replace Toner "On the Fly"







Leading innovation where it counts the most.

When customers talk, we not only listen, we work to find innovative ways to meet their requirements. Hence, some of our most advanced innovations are in areas of greatest interest to Toshiba's loyal customers. Some of these areas include top-notch security, energy savings, performance, image quality, and enhanced features.

Energy superstar

Creating environmentally responsible products is among our greatest technological achievements. The e-STUDIO555/655/755/855 Series is Energy Star, ISO-14001, ISO-9001, and RoHS compliant—not to mention lead-free, halogen-free, and chromiumfree. Various user features offer energy savings, like our Super Sleep Mode which uses just one watt of power. In addition, product manuals are provided in electronic form to reduce waste. Our involvement in conservation programs includes Close the Loop, a zero waste to landfill initiative. Your local Toshiba representative can provide further details on these programs.

The security of owning Toshiba

Using advanced Toshiba technology, the e-STUDIO555/655/755/855 Series keeps your data secure from any outside threat while enabling you to restrict internal access as well. AES 128-bit encryption comes standard to encrypt all data on the system's built in 60 GB hard disk drive. An optional data disk overwrite further ensures security by overwriting data on the hard drive multiple times. Authentication can be configured to require login for access to the device, as well as access to specific features and functions. Toshiba's proprietary operating system adds yet another level of protection. Other top security measures include IP Filtering to prevent unauthorized visitor access, wireless encryption protocol, and optional IPSec.

e-BRIDGE™, the 3rd Generation

Since its inception, Toshiba e-BRIDGE technology has provided multifunction performance that is unsurpassed. In its third generation, this single board architecture combines copy, print, scan and other functions. Advanced scanning is available to instantly and automatically convert scanned documents into 17 different formats, including MS Word, MS Excel and Searchable PDF.

secureMFP

- > Secures Print Output
- > Secures Data
- > Creates Secure PDF
- > Controlled Access



Competitive edge or unfair advantage?

At a time when the economy is shifting and businesses are cutting back, there are new opportunities to operate with greater efficiency. The Toshiba e-STUDIO555/655/755/855 Series enables you to make all of your employees more productive, while reducing costs significantly.

Everything you're looking for

The e-STUDIO555/655/755/855
Series has it all, and more. Improved ease of use is obvious when you first walk up to the large, full color 8.5"
WVGA touch screen. In addition to a multitude of common as well as unique functions, you'll also find a complete selection of finishing options.

Speaking of unique, one finishing option even allows you to saddle stitch booklets using letter, legal or ledger sized paper. Scan ahead of time, if need be, multiple copy jobs in advance. Or take advantage of a vast array of efficient features and options such as secure Bluetooth short range wireless printing, automatic status notification sent to IT, facilities, or dealers, and a fax feature that includes the option of a second line, just to name a few.

The Managed Print Experts

At Toshiba, we've moved far beyond the box. Our people bring innovative, real-world solutions to all your print management needs. We'll help you cut costs, secure your documents and reduce your environmental footprint. And if there's one thing every business and our planet can use right now, it's managing to do more with less.

See for yourself. Call or visit your nearest Toshiba dealer. Let us show you how to gain a competitive edge, or an unfair advantage—whichever way you care to look at it.











- > 8.5" Color Touch Screen
- > Saddle Stitch Booklets
- > Scan-Ahead Feature
- > Bluetooth Wireless





©-STUDIO 555/655/755/855





- > Black & White MFP
- > Up to 85 PPM
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly

Specifications

Copying Process/Type IEPM (Dry Process)/Laser Technology

Original Reading Method CCD Line Sensor Copy/Print Resolution 2400 x 600 dpi Gradation 256 Steps Copy/Print Speed 55 / 65 / 75 / 85 cpm Warm-Up Time Appx 130 Seconds

First Copy Time eS555/655: Less Than 4.0 Seconds (Letter-Size) eS755/855: Less Than 3.5 Seconds (Letter-Size)

Duty Cycle 460K/515K/540K/600K Multiple Copying Up to 9,999 Copies

Standard Paper Supply 2 x 500-Sheet Drawer; 2 x 1,250-Sheet Tandem Drawer;

100-Sheet Stack Feed Bypass

Maximum Paper Supply Up to 7,600 Sheets (w/Optional 4,000-Sheet LCF) Acceptable Paper Size Cassette: Statement-R to Ledger (17-110 lbs.)

Bypass: Statement-R to 11" x 17" (17-110 lbs.)

LCF: Letter Only (17-110 lbs.) Std. Bond, Post Card

Special Paper Tab Sheets - Bypass + 1/2 Drawers

Memory 1GB RAM, 60 GB HDD

Reduction/Enlargement 25% to 400%

100-Sheet Stack Feed Bypass **Bypass Tray** Control Panel 8.5" Wide VGA Color Touch-Screen Dimensions Appx. 28" x 31" x 46" (W x D x H)

Weight Appx. 462 lbs. Power Supply 120 Volts; 20 Amps Power Consumption Maximum 2 0kW 460K / 515K / 540K / 600K PM Cycle Black Toner Yield 62 4K Impressions Drum Type/Yield 460K / 515K / 540K / 600K Developer Yield 460K/515K/540K/600K

Print (Standard)

Print Speed 55 / 65 / 75 / 85 ppm PDL Support PCL6, PostScript3, XPS

Operating Systems Windows 2000/XP/2003/Vista/2008

Mac X OS 10.2.4/10.3/10.4/10.5

UNIX, Linux, CUPS Protocol Support IPX/SPX, TCP/IP (IPV4/V6)

EtherTalk, AppleTalk PAP, LPR/LPD IPP w/Authentication, Port 9100 Bluetooth, SMB, Netware

Drivers Windows 2000/XP/2003/Vista/2008

Mac X OS 10.2.4/10.3/10.4/10.5 (OS 10.4 PPD)

UNIX, Linux, AS/400, SAP R/3 Connectivity Ethernet 10/100BaseT

USB 2.0, 802.11b/g Wirelesss LAN

Bluetooth (HCRP)

Device Management TopAccess

WHQL, Novell, HPOS (Dazel), Vista Premium Certification

Scan (Standard)

Scan Speed 80 spm LT-Size @300 dpi

Scan Resolution 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi

File Format TIFF, PDF, JPEG, XPS.

MS Word, MS Excel, Searchable PDF w/ Adv. Scanning option

Authentication LDAP, SMTP, Windows Server Domain

E-Filing (Standard)

Operation Method Color Touch Screen Control Panel or Client PC

1 Public Box; 200 Private User Boxes Number of Boxes

Capacity of Boxes 100 Folder per Box 400 Documents per Folder 1000 Pages per Documents

Facsimile Option

Compatibility Super G3 G3 Data Compression MH/MR/MMR/JBIG

Transmission Speed Appx. 3 Seconds per Page Fax Modem Speed 33.6 Kbps

Fax Memory Transmission 500MB (HDD)

Reception 500MB (HDD) Backup Permanent (HDD)

Memory Transmission 100 Jobs; 1,000 Destinations Max; 400 Destinations/Job

Scan Speed 0.7 Seconds per Page; 50 Scans per Minute

Other Fax Functions Internet Fax; Network Fax

Accessories (Options)

Finishing Options

50-Sheet Stapler Console Finisher MJ1027 50-Sheet Saddle-Stitch Finisher MJ1028 100-Sheet Saddle-Stitch Finisher MJ1029 Rails for Finisher KN1017 2 or 3 Hole Punch Unit MJ6003 Post Inserter Unit M.J7001

Additional Paper Options

4,000-Sheet LT-Size Large Capacity Feeder MP4004

Connectivity/Security Options

GD1250 Fax Kit 2nd Line Fax GD1260 Wireless LAN Adapter GN1050 Bluetooth Module GN2010 Antenna GN3010 Data Overwrite Kit GP1070 IPSec Kit GP1080 Meta Scan Enabler GS1010 External Interface Enabler GS1020 Advanced Scanning GB1280T

Miscellaneous Options

KP2004 HID/Mifare Card Reader Mifare Reader Option KP2005 Harness Kit for Coin Controller GQ1240

















Corporate Office 2 Musick, Irvine, CA 92618-1631

Tel: 949-462-6000

East Coast 959 Route 46 East, 5th Floor, Parsippany, NJ 07054

Tel: 973-316-2700

Midwest 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631

Tel: 773-380-6000

South 2037 Bakers Mill Rd., Dacula, GA 30019

Tel: 678-546-9385

142 Technology, Suite 150, Irvine, CA 92618 West Coast

Tel: 949-462-6262

Web Site www.copiers.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

© 2009 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv. Code: ES5556557558551